Femtowatt Photoreceiver with InGaAs-PIN Photodiode



The picture shows model FWPR-20-IN-FS.

The photoreceiver will be delivered without post holder and post.


Features

- InGaAs-PIN photodiode, 0.5 mm active diameter
- Ultra low noise, NEP 7.5 fW/√Hz
- Amplifier transimpedance gain 1 x 10¹¹ V/A
- Max. conversion gain 0.95 x 10¹¹ V/W @ 1550 nm
- Spectral range 900 1700 nm
- Free-space input 1.035"-40 threaded, alternatively 25 mm diameter unthreaded
- Easily convertible to fiber optic input (FC and FSMA) with optionally available screw-on adapters
- UNC 8-32 and M4 tapped holes for mounting on standard posts with metric and imperial thread

Applications

- Fluorescence measurements
- NIR spectroscopy
- Electrophoresis
- Replacement for (liquid nitrogen) cooled Ge photodiodes and avalanche photodiodes (APDs)

Block Diagram



SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

F E MT O

Femtowatt Photoreceiver with InGaAs-PIN Photodiode

Available Versions

FWPR-20-IN-FST



Picture shows 1.035"-40 threaded flange with internally threaded coupler ring (outer diameter 30 mm)

1.035"-40 threaded flange for free space applications, compatible with many optical standard accessories and for use with various types of fiber connector adapters.

Optionally available:

Fiber adapters PRA-FC, PRA-FCA and PRA-FSMA. The coupling efficiency will depend on fiber type. With the relative large 0.5 mm dia. photodiode installed in the FWPR-20-IN input coupling is not critical. However, standard SM 9/125 fibers (PC or APC) with low numerical aperture (NA) are recommended for ensuring near 100% coupling efficiency.

FWPR-20-IN-FS



Picture shows unthreaded flange with 25 mm diameter

25 mm dia. unthreaded flange for free space applications. Compatible with many optical standard accessories.

Related Models

FWPR-20-SI-FST

FWPR-20-SI-FS

Si photodiode, 1.1 \times 1.1 mm 2 , 320 - 1100 nm free space input, 1.035"-40 threaded flange

Si photodiode, 1.1 \times 1.1 mm², 320 - 1100 nm free space input, 25 mm dia. unthreaded flange

Available Accessories

PRA-FC PRA-FCA PRA-FSMA







Fiber-adapter with external 1.035"-40 thread (suitable for FST models only).

PRA-PAP



Alternative mounting option: Post adapter plate, easy to mount on FEMTO photoreceiver series OE, FWPR, PWPR, HCA-S and LCA-S.

PS-15-25-L



Power supply Input: 100 – 240 VAC Output: ±15 VDC

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

FEMTO

FWPR-20-IN_R6/TH,JMa,UH/21MAR2022 Page 2 of 6

Femtowatt Photoreceiver with InGaAs-PIN Photodiode

Test conditions $V_S = \pm 15 \text{ V}$, $T_A = 25 \, ^{\circ}\text{C}$, output load impedance 1 M Ω , Specifications

warm-up 20 minutes (min. 10 minutes recommended)

Gain Transimpedance gain 1.0×10^{11} V/A (@ output load ≥ 100 k Ω)

±1 % (electrical) Gain accuracy

 0.95×10^{11} V/W typ. (@ 1550 nm, output load $\geq 100 \text{ k}\Omega$) Conversion gain

Frequency Response Lower cut-off frequency

Upper cut-off frequency (-3 dB) 20 Hz (±20 %)

Time Response Rise/fall time (10 % - 90 %) 18 ms (±20 %)

Noise equivalent power (NEP) 7.5 fW/√Hz (@ 1550 nm, 1 Hz) Input

> Optical saturation power 110 pW (for linear amplification, @ 1550 nm)

InGaAs-PIN photodiode Detector Detector

> Active area \varnothing 0.5 mm Spectral range 900 - 1700 nm

Max. sensitivity 0.95 A/W typ. (@ 1550 nm)

Output Output voltage range $-1.6 \text{ V} \dots +10 \text{ V}$ (@ ≥ 100 kΩ output load)

Offset compensation range ±1.6 V typ. (adjustable by offset potentiometer) Output impedance 50 Ω (terminate with \ge 100 kΩ load)

Max. output current 25 mA (short-circuit proof)

Output noise 3 mV_{RMS} (20 mV_{PP}) typ. ($@ \ge 100 \text{ k}\Omega$ load, no signal on

detector, measurement bandwidth 8 kHz)

Material Input Flange 1.4305 stainless steel, nickel-plated (FST flange)

AlMg4.5Mn, nickel-plated (FS flange)

Material 1.4305 stainless steel, glass bead blasted Coupler Ring

(FST version only)

Power Supply Supply voltage

> Supply current ± 15 mA (depends on operating conditions,

> > recommended power supply capability min. ±50 mA)

203 g (0.45 lbs) FWPR-20-IN-FST incl. coupler ring Case Weight

190 g (0.42 lbs) FWPR-20-IN-FS

±15 V (±14.5 V ... ±16.5 V)

AlMg3/4.5Mn, nickel-plated Material

Temperature Range Storage temperature -30 °C ... +85 °C

0 °C ... +60 °C Operating temperature

Absolute Maximum Ratings Optical input power (CW) 10 mW

±20 V Power supply voltage

Femtowatt Photoreceiver with InGaAs-PIN Photodiode

Connectors FWPR-20-IN-FST 1.035"-40 threaded flange for Input free space applications and for use with various types of optical standard accessories FWPR-20-IN-FS 25 mm dia. unthreaded flange for free space applications Output BNC jack (female) LEMO® series 1S, 3-pin fixed socket Power supply (mating plug type: FFA.1S.303.CLAC52) PIN 2 Pin 1: +15 V Pin 2: -15 V PIN 3 Pin 3: GND GND Scope of Delivery FWPR-20-IN, internally threaded coupler ring (FST version only), LEMO® 3-pin connector, datasheet, transport package Ordering Information FWPR-20-IN-FST 1.035"-40 threaded flange for free space applications and for use with various types of optical standard accessories. FWPR-20-IN-FS 25 mm dia. unthreaded flange for free space applications. Spectral Responsivity 1.0 0.8 Photo Sensitivity (A/W) 0.6 0.4 0.2 900 1000 1100 1200 1300 1400 1500 1600 1700 1800 800 Wavelength (nm) DB-Sens-FWPR-20-IN R01

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY


F E M T O


FWPR-20-IN_R6/TH,JMa,UH/21MAR2022 Page 4 of 6

Femtowatt Photoreceiver with InGaAs-PIN Photodiode

Dimensions

FWPR-20-IN-FST (1.035"-40 threaded free space input)





FWPR-20-IN-FST_R1

all dimensions in mm unless otherwise noted

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY


F E M T O


FWPR-20-IN_R6/TH,JMa,UH/21MAR2022 Page 5 of 6

Femtowatt Photoreceiver with InGaAs-PIN Photodiode

Dimensions (continued)

FWPR-20-IN-FS (25 mm dia. unthreaded free space input)





FWPR-20-IN-FS_R1

all dimensions in mm unless otherwise noted

FEMTO Messtechnik GmbH Klosterstr. 64 10179 Berlin · Germany Phone: +49 30 280 4711-0 Fax: +49 30 280 4711-11 Email: info@femto.de www.femto.de Specifications are subject to change without notice. Information provided herein is believed to be accurate and reliable. However, no responsibility is assumed by FEMTO Messtechnik GmbH for its use, nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of FEMTO Messtechnik GmbH. Product names mentioned may also be trademarks used here for identification purposes only.

© by FEMTO Messtechnik GmbH · Printed in Germany

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

F E T O

FWPR-20-IN_R6/TH,JMa,UH/21MAR2022 Page 6 of 6