Datasheet LCA-S-400K-IN

Low Noise 400 kHz Photoreceiver with InGaAs-PIN Photodiode



The picture shows model LCA-S-400K-IN-FS. The photoreceiver will be delivered without post holder and post.


Features

- InGaAs-PIN photodiode, 0.5 mm active diameter
- Bandwidth DC 400 kHz
- Amplifier transimpedance gain 1.0 × 10⁷ V/A
- Max. conversion gain 9.5 × 10⁶ V/W @ 1550 nm
- Spectral range 900 1700 nm
- Free-space input 1.035"-40 threaded, alternatively 25 mm diameter unthreaded
- Easily convertible to fiber optic input (FC and FSMA) with optionally available screw-on adapters
- UNC 8-32 and M4 tapped holes for mounting on standard posts with metric and imperial thread

Applications

- NIR Spectroscopy
- General purpose opto-electronic measurements
- Optical front-end for oscilloscopes, A/D converters and lock-in amplifiers

Block Diagram



SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

F E MT O

Low Noise 400 kHz Photoreceiver with InGaAs-PIN Photodiode

Available Versions

LCA-S-400K-IN-FST



Picture shows 1.035"-40 threaded flange with internally threaded coupler ring (outer diameter 30 mm)

1.035"-40 threaded flange for free space applications, compatible with many optical standard accessories and for use with various types of fiber connector adapters.

Optionally available:

Fiber adapters PRA-FC, PRA-FCA and PRA-FSMA. The coupling efficiency will depend on fiber type. With the relative large 0.5 mm dia. photodiode installed in the LCA-S-400K-IN input coupling is not critical. However, standard SM 9/125 fibers (PC or APC) with low numerical aperture (NA) are recommended for ensuring near 100% coupling efficiency.

LCA-S-400K-IN-FS



Picture shows unthreaded flange with 25 mm diameter

25 mm dia. unthreaded flange for free space applications. Compatible with many optical standard accessories.

Related Models

LCA-S-400K-SI-FST

LCA-S-400K-SI-FS

Si-PIN, \varnothing 3 mm, 320 - 1060 nm free space input, 1.035"-40 threaded flange

Si-PIN, \varnothing 3 mm, 320 - 1060 nm free space input, 25 mm dia. unthreaded flange

Available Accessories

PRA-FC PRA-FCA PRA-FSMA







Fiber-adapter with external 1.035"-40 thread (suitable for FST models only).

PRA-PAP



Alternative mounting option: Post adapter plate, easy to mount on FEMTO photoreceiver series OE, FWPR, PWPR, HCA-S and LCA-S.

PS-15-25-L



Power supply Input: 100 – 240 VAC Output: ±15 VDC

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

EMTO

Datasheet LCA-S-400K-IN

Low Noise 400 kHz Photoreceiver with InGaAs-PIN Photodiode

Specifications $V_S = \pm 15 \text{ V}, T_A = 25 \text{ °C}, \text{ output load impedance 1 M}\Omega,$

warm-up 20 minutes (min. 10 minutes recommended)

Gain Transimpedance gain $1.0 \times 10^7 \text{ V/A } (@ \text{ output load } \ge 100 \text{ k}\Omega)$

Gain accuracy ± 1 % (electrical)

Conversion gain $9.5 \times 10^6 \text{ V/W typ.}$ (@ 1550 nm, output load $\geq 100 \text{ k}\Omega$)

Frequency Response Lower cut-off frequency DC Upper cut-off frequency (–3 dB) 400 kHz

Gain flatness ±0.5 dB

Time Response Rise/fall time (10 % - 90 %) 1 μ s

Input Noise equivalent power (NEP) 75 fW/√Hz (@ 1550 nm, 10 kHz)
Optical saturation power 1 μW (for linear amplification, @ 1550 nm)

Input offset compensation range ±300 nA, adjustable by offset potentiometer

Detector Detector InGaAs-PIN photodiode

Active area \varnothing 0.5 mm Spectral range 900-1700 nm

Max. sensitivity 0.95 A/W typ. (@ 1550 nm)

Output Output voltage range $-3 \text{ V} \dots +10 \text{ V} \text{ (}@ \geq 100 \text{ k}\Omega \text{ output load)}$

Output impedance 50 Ω (terminate with \geq 100 k Ω load)

Max. output current 30 mA (short-circuit proof)

Output noise 2 mV_{RMS} (12 mV_{PP}) typ. (@ \geq 100 k Ω load, no signal on

detector, measurement bandwidth 1 MHz)

Input Flange Material 1.4305 stainless steel, nickel-plated (FST flange)

AlMg4.5Mn, nickel-plated (FS flange)

Coupler Ring Material 1.4305 stainless steel, glass bead blasted

(FST version only)

Power Supply Supply voltage

Supply current ± 40 mA (depends on operating conditions,

recommended power supply capability min. ±150 mA)

Case Weight 212 g (0.47 lbs) LCA-S-400K-IN-FST incl. coupler ring

195 g (0.43 lbs) LCA-S-400K-IN-FS

±15 V (±14.5 V ... ±16.5 V)

Material AIMg4.5Mn, nickel-plated

Temperature Range Storage temperature —30 °C ... +85 °C

Operating temperature 0 °C ... +60 °C

Absolute Maximum Ratings Optical input power (CW) 10 mW

Power supply voltage $\pm 20 \text{ V}$


F E T O

Datasheet LCA-S-400K-IN

Low Noise 400 kHz Photoreceiver with InGaAs-PIN Photodiode

Connectors LCA-S-400K-IN-FST Input 1.035"-40 threaded flange for free space applications and for use with various types of optical standard accessories LCA-S-400K-IN-FS 25 mm dia. unthreaded flange for free space applications Output BNC jack (female) LEMO® series 1S, 3-pin fixed socket Power supply (mating plug type: FFA.1S.303.CLAC52) PIN 2 Pin 1: +15 V Pin 2: -15 V PIN 3 Pin 3: GND GND Scope of Delivery LCA-S-400K-IN, internally threaded coupler ring (FST version only), LEMO® 3-pin connector, datasheet, transport package Ordering Information LCA-S-400K-IN-FST 1.035"-40 threaded flange for free space applications and for use with various types of optical standard accessories. LCA-S-400K-IN-FS 25 mm dia. unthreaded flange for free space applications.

Spectral Responsivity




SOPHISTICATED TOOLS FOR SIGNAL RECOVERY


Datasheet LCA-S-400K-IN

Low Noise 400 kHz Photoreceiver with InGaAs-PIN Photodiode

Dimensions

LCA-S-400K-IN-FST (1.035"-40 threaded free space input)





DZ_LCA-S-400K-IN-FST_R1

all dimensions in mm unless otherwise noted


SOPHISTICATED TOOLS FOR SIGNAL RECOVERY


F E MT O

Low Noise 400 kHz Photoreceiver with InGaAs-PIN Photodiode

Dimensions (continued)

LCA-S-400K-IN-FS (25 mm dia. unthreaded free space input)





DZ_LCA-S-400K-IN-FS_R1

all dimensions in mm unless otherwise noted

FEMTO Messtechnik GmbH Klosterstr. 64 10179 Berlin · Germany Phone: +49 30 280 4711-0 Fax: +49 30 280 4711-11 Email: info@femto.de www.femto.de Specifications are subject to change without notice. Information provided herein is believed to be accurate and reliable. However, no responsibility is assumed by FEMTO Messtechnik GmbH for its use, nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of FEMTO Messtechnik GmbH. Product names mentioned may also be trademarks used here for identification purposes only.

© by FEMTO Messtechnik GmbH · Printed in Germany

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

F E M T O